



FoamPro Electronic Off-Board Pick-up Kit Detailed Specifications

Special Note: When preparing specifications for your new foam proportioning system, assure the proper use of the FoamPro system by incorporating these specifications as written. No competitive foam proportioning system can match FoamPro for performance.

The apparatus shall be equipped with an electronically-operated selector kit with flush. The kits are designed to connect one or two on-board concentrate reservoir(s) and an off-board pickup concentrate source into your FoamPro proportioning system. The kit provides an automatic source selection control and an automatic 8 second water flush cycle to cleanse the lines between source selections. The system includes an electronic control box, panel interface switches and LED lamps, controller interface cable, control valves, line strainers, check valves, off-board pickup panel plate and pickup hose and wand. Kits are available in 1" or 1 ½" ID and for 12 VDC or 24VDC power. **Kits are available for usage on 2002, 3012, 3020 SP and 3040 SP models only.**



26 Southern Blvd. • Nesconset, NY 11767 USA
Phone 800-533-9511 • FAX 816-892-3178
www.foampro.com